


TITANIUM EARMOLDS REWORKING


SMALL BURR 20.000 – 50.000 RPM

Ideal for reworking small or tight areas with minimal material removal, producing an especially fine grinding pattern.




LARGE BURR 20.000 – 50.000 RPM

Ideal for reworking larger areas and surfaces with increased material removal, producing a fine grinding pattern.




POLISHING LENS 6.000 – 15.000 RPM

For polishing and smoothing surfaces with low to medium material removal, achieving an extremely smooth and shiny surface.



POLISHING ROLLER 6.000 – 15.000 RPM

For polishing and smoothing surfaces with low to medium material removal, achieving an extremely smooth and shiny surface.



HOLDER

For securing polishing lenses/discs.



SPINDLE HOLDER

For use with polishing rollers.



DRESSING DIAMOND

For dressing, balancing, and shaping polishers.



TITANI